

# S-Max pico

## Optic

- Stainless Steel Body • ISB Turbine • Cellular Glass Optics
- Ceramic Bearings • Clean Head System • Single Spray

Power : 9 W, Speed : 380,000~450,000 min<sup>-1</sup>, Head Size : ø8.6 x H9.0 mm

For short shank burs/ ultra short shank burs ■ Accessory bur set

Connect Direct to KaVo®, Sirona®, W&H®, Bien-Air® Couplings



# S-Max pico

Expanded Operational Visibility and Dexterity



S-Max pico

Ti-Max X600L

## Spare Parts

MODEL	PRODUCTS	ORDER CODE	MODEL	PRODUCTS	ORDER CODE	MODEL	PRODUCTS	ORDER CODE
SX-PU03	Cartridge for S-Max pico	P1140200	SX-PU04	Head cap for S-Max pico	P1140500	SX-PU05	Head cap wrench for S-Max pico	20002803

KaVo® and MULTiflex® LUX are registered trademarks of Kaltenbach & Voigt GmbH & Co. Sirona® is a registered trademark of Sirona Dental Systems GmbH. W&H® is a registered trademark of W&H Dentalwerk Bümmoes GmbH. Bien-Air® and Unifix® are registered trademarks of Bien-Air Dental S.A.



Washable in the thermodisinfectant



Autoclavable up to 135°C

NAKANISHI INC.	NSK Europe GmbH	NSK United Kingdom Ltd	NSK Dental LLC	NSK Oceania Pty Ltd	NSK Middle East	NSK Asia Pte Ltd
www.nsk-inc.com	www.nsk-europe.de	www.nsk-uk.com	www.nskdental.com	www.nskoceania.com.au	www.nsk-inc.com	www.nsk-inc.com
700 Shimohinata Kanuma-shi Tochigi 322-8666, Japan TEL : +81 (0)289-64-3380 FAX : +81 (0)289-62-5636	Elly-Beinhorn-Strasse 8 65760 Eschborn, Germany TEL : +49 (0)6196 77606-0 FAX : +49 (0)6196 77606-29	Office 5, Gateway1000, Arlington Business Park, Whittle Way, Stevenage, SG1 2FP, UK TEL : +44 (0)1438 310670 FAX : +44 (0)1438 310671	1800 Global Parkway Hoffman Estates, IL 60192, USA TEL : +1 888 675 1675 FAX : +1 800 838 9328	Unit 22, 198-222 Young St. Waterloo, Sydney, NSW 2017, Australia TEL : +61 (0)2 8306 3000 FAX : +61 (0)2 8306 3030	Room 6EA-701, 7th Floor, East Wing No.6 Dubai Airport Free Zone, PO Box 54316 Dubai, UAE TEL : +971 (0)4-204-5507 FAX : +971 (0)4-204-5508	1 Maritime Square, #09-33 HarbourFront Centre, Singapore 099253 TEL : +65-6376-5018 FAX : +65-6376-0233

Specifications are subject to change without notice.

REF PR-D654E Ver.2 13.00.00.00



# S-Max pico

The innovative air turbine with ultra mini head and super slim body shape

The NSK S-Max pico series has been developed for the operation of Minimal Intervention (M.I.). The ultra mini head and super slim handpiece design is the result of fine NSK precision engineering allowing a wider view of the operational field, and greater flexibility for dexterity.

- Stainless Steel Body
- ISB Turbine
- Cellular Glass Optics
- Ceramic Bearings
- Clean Head System
- Single Spray

Power : 9 W, Speed : 380,000~450,000 min<sup>-1</sup>, Head Size : ø8.6 x H9.0 mm

For short shank burs/ ultra short shank burs ■ Accessory bur set

Connect to NSK Couplings  



Optic MODEL S-Max pico ORDER CODE P1140

## ■ Improve the accuracy of operation with the microscope



The ultra mini head delivers expanded operational visibility and greater flexibility. Patient comfort is increased.

In combination with mirror technique



## pico bur Dedicated burs for S-Max pico series

NSK has developed special ultra short shank burs to operate specifically with the pico handpiece. These high quality precision burs are concentric and durable. Use of NSK ultra short shank burs maximizes the mini advantage of the pico handpiece.













Original bur of high precision (Rotational speed: 400,000/min<sup>-1</sup>)





Accessory bur set (PC1-6/six-pack)

## pico bur Product lineup

	MODEL <b>PC1</b> ORDER CODE <b>Y1001817</b> • Pack of 3		MODEL <b>PC6</b> ORDER CODE <b>Y1001822</b> • Pack of 3
	MODEL <b>PC2</b> ORDER CODE <b>Y1001818</b> • Pack of 3		MODEL <b>PC3ff</b> ORDER CODE <b>Y1002019</b> • Extra fine bur • Pack of 3
	MODEL <b>PC3</b> ORDER CODE <b>Y1001819</b> • Pack of 3		MODEL <b>PC4ff</b> ORDER CODE <b>Y1002020</b> • Extra fine bur • Pack of 3
	MODEL <b>PC4</b> ORDER CODE <b>Y1001820</b> • Pack of 3		MODEL <b>PC5ff</b> ORDER CODE <b>Y1002021</b> • Extra fine bur • Pack of 3
	MODEL <b>PC5</b> ORDER CODE <b>Y1001821</b> • Pack of 3		MODEL <b>PC6ff</b> ORDER CODE <b>Y1002022</b> • Extra fine bur • Pack of 3

## ■ Size specifications of the S-Max pico series




▲ Comparison of body sizes



### Cartridge Replacement

Cartridges are easily replaced in your practice helping you to control cost and down-time. The replacement cartridge incorporates the spray holes to guarantee cartridge and water spray always work well together.



### Water Spray & Cellular Optics

The NSK Water Spray effectively cools the entire operating field whilst the cellular glass optic rod delivers light exactly where it is needed.